




HWY8t MULTIFUNCTIONAL ELECTRIC BED




Healthward`



Product data sheet

HWY8t

FEATURES AND HIGHLIGHTS



Technical parameters

• External size (LxW):	2140x1060 mm
Mattress platform:	1925x900 mm
Safe working load:	250 kg
Height adjustment:	480-770 mm
Back-rest adjustment:	0-75° (±10°)
Knee-rest adjustment:	0-35° (±10°)
Reverse trendelenburg:	0-12°
Trendelenburg:	0-12°
Angle indicator:	0-90°
Position line:	30°
Voltage and frequency:	100-240 V · 50/60 Hz
Plug as required (hospital grade)	

Optional

Hand controller
U Weighing system
□ Nurse control panel
Cardiac chair position
Bed extension 20cm
Back-up battery
Directional wheels function
ABS mattress stopper
☐ Monkey pole
Balkan frame
Linen holder

Technical configuration

☑ Linear motor	4 pcs
☑ 5'' double side castors, central locking system	4 pcs
ABS Oasis side rail extra height	1 set
ABS Oasis bed ends with safe lock	1 set
☑ Stamping forming bed platform	1 pc
Plastic socket inside pp guardrail for phone or glasses	2 pcs
Patent angle indicator for back-rest and trendelenburg position	4 pcs
🗹 Ø70mm wall bumper wheel	4 pcs
☑ IV pole	1 set
☑ IV pole prevision	4 pcs
🗹 Drainage hook	2 pcs
Central locking pedal	2pcs
Emergency stop button	1 pc
🗹 Manual CPR	
Z Electric CPR	


Go button Use the GO button to activate the bed; protects the patient against an injury caused by any unintentional movement of the bed. Control system is automatically locked after 3 min. One button mobilisation position Respects easy patient mobilisation: One-button for patient mobilisation

position -back plate raised, double hole design on back part guardrail, which supports patient self standing.

Lowest position indicator

The lowest position indicator design allows the medical staff to observe the bed safe position during night or long distance; blue light indicate lowest bed height, otherwise it's yellow.





Great multi-care

Respects easy patient mobilisation: One-button for patient mobilisation position -back plate raised, double hole design on back part guardrail, which supports patient self standing.

Steels | Painting

Baosteel from Fortune Global 500. 11 Process epoxy painting, ASTM testing anti-baterial, paint thickness 0.12 mm, brightness 60°, paint can resist 50 kg impact.





Safety

IEC60601 Safty Standard. One-button emergency stop switch can quickly stop all going movement.

Wheels

Castors with TPR tire, no worn-out after running 30KM, united forming without bolts. Pass Dynamic test: Bearing 120kg run 30KM and pass obstacles 500time.

Bed Surface

Stamping forming platform, smooth surface no welding scar, bearing 250 kg load. Option ABS platform and resin X-ray translucent platform.

Head & foot board

Detachable PP head&foot board(Y19), with medical record card on foot panel, patent design, using the eccentric locking structure, one step quick removable.

Siderail controller

Controls in the siderails: Numerous studies located in the sideralis: Numerous studies that a source on troller is the sideralis is easier to reach, allowing the patient to adjust the basic position of the bed through the controller. It is different between inside and outside, more safe and scientific.



Stainless Steel Column with plastic hook.





Welding | Chassis

Panasonic robotic ensure, 360° full smooth wedlding. Solid bed base made of 5.0 mm stamped rotating plate.



Electric motor

Linear motor, with UL/ROHS/EN standard. Noise under 50 dB, with lifetime 20,000 times movement.

CPR

CPR emergency reset handle to immediately flatten the bed back part; located on both sides of the bed. Electric CPR button is setted inside control panel, one button to make the back plate flat.



Brake

Three position braking systerm, transporting can maintain a straight line.

Patent angle indicator, clearly show back-rest and tredelenbug position.



Siderail

4 pcs PP siderail (T20), with patent angle indicators on each one, clearly show back-rest and tredelenburg position.

Wall bumper wheel Φ70mm bumper wheels at the outermost periphery of the bed to protect the bed and wall, anti-, collision and endurable.

Drainage hooks Mobile plastic drainage hooks.













Healthward `





♀ 17800 CASTLETON ST STE 180.CITY OF INDUSTRY CA 91748

export@health-ward.com

() www.health-ward.com

