HW-EX123 SUCTION DEVICE



Healthward`



HW-EX123

FEATURES AND HIGHLIGHTS

Technical parameters

 Power voltage 	AC110-220V±22V	
Rated frequency	50-60Hz	
 Suction pump 	Oil-free piston pump	
Negative pressure	≥0.09MPa(680mmHg)	
Range of negative pressure	0.02MPa-limit negative pressure value	
Noise	≪60dB	
Suction rate	≥20L/Min	
 Storage bottle capacity 2500mL/piece, set of 2, high temperature resistant glass 		
 Intermittent loading continuous operation Short operation time, maximum operation time 30min, duration 50% 		
 Classification of safety protection Class I equipment, type B applied part 		
Environmental temperature ra	nge -40~60°C	
Relative Humidity Range	≪90%	
Atmospheric pressure range	500~1060hPa	
 Weight 	13kg	
 Package size 	450×400×600mm	

Technical configuration

\blacksquare Suction flexible catheter(length 2M, Φ 7×13)	1 pc
🗹 Empty foot switch	1 pc
🗹 Air filter	2 pcs
🗹 Fuse	2 pcs
☑ Chest suction tube	1 pc



Feature

Low noise, maintenance-free, high pumping rate, fast negative pressure rise, no oil mist pollution.

Design

Portable medical suction device, easy to move, compact and flexible.

Structure feature

The product structure primarily consists of piston pump, vacuum gauge, negative pressure regulating valve, air filter, storage bottle, and foot pedal switch.

Working principle

Utilizing a high-efficiency piston pump, it operates without the need for oil lubrication, ensuring long-term operation and has a long service life. The structure is rational and will not generate positive pressure, absolutely guaranteeing safety.

Piston pump

Utilizing a high-efficiency piston pump, it operates without the need for oil lubrication, enabling long-term operation and has a long service life.

Shell material

Featuring an ABS injection-molded shell, it has an attractive appearance, stable and durable, and ease of cleaning.



Puller

Carbon steel spray plastic puller, welded firmly, easy to push, suitable for regional transit.



Handle

Fixed, portable handle for easy lifting, saving time and effort.



Vacuum gauge

Using high precision vacuum pressure gauge, direct display of negative pressure value.



Negative pressure regulating valve

Any negative pressure value can be selected within the limit range for easy operation. Negative pressure adjustment range: 0.02-0.09MPa (680mmHg).



Storage bottle

Large caliber, large-capacity liquid storage bottle, made of glass, easy to clean, with a sealing ring stopper, good sealing, easy to open. The bottle is equipped with an overflow protection device to prevent dirty liquid from flowing into the pump body.



Air filter

Air filter reduce air pollution of the surrounding environment from dirty liquids.



Caster

 $4 \phi 50$ mm diameter mobile casters, 2 with lock, easy to move.



Switch

Foot switch, manual switch for low voltage control, and fully sealed, safe and reliable. Foot switch sensitivity, low voltage control, 12V.



Healthward`

As the circumstance of printing, the photos might have minor difference on color, tactile from real products. As the update of design and improvement, parameters and outlook of products might change, thanks for understanding.



- 2 17800 CASTLETON ST STE 180.CITY OF INDUSTRY CA 91748
- export@health-ward.com
- () www.health-ward.com



ieneral catalogue